









SPECIFICATIONS:

- Material:
 - Body: PA66
 - Terminal: Brass
- Wire range: N/A
- Electrical rating: 300V, 8A.
- Max Torque: N/A.
- Wire strip length: N/A.
- Operating temperature: -40C to +105C.
- $A = (N \times P) + 1.39\text{MM}$
- $B = (N - 1) \times P$
- $P \text{ (PITCH)} = 3.81\text{MM} (.150")$
- $N = \text{Number of positions available 2 through 20.}$

ENTER DESCRIPTION EC NO: NEO2006-0310 DRAWN: LROTHAUS 2006/01/09 CHKD: CYORK 2006/01/09 APPR: JPAWLICK 2006/01/10 A			DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 4:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
					mm		INCH		DRAWN BY LROTHAUS	DATE 12/6/05	TITLE 3.81MM, EURO HEADER RIGHT ANGLE, CLOSED END		
					4 PLACES ± --- ±.0015		CHECKED BY C. YORK		DATE 01/06/06				
					3 PLACES ±0.038 ±.005		APPROVED BY		DATE				
					2 PLACES ±0.13 ±.01		MATERIAL NO.		DOCUMENT NO.				
					1 PLACE ±0.3 ±---		SEE CHART		SD-39512-001				
					ANGULAR ± 2 °		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. 1 OF 1						

