




Pos.4

Pos.1

P1

1

2

8

3

25.0±5.0

6

LABEL

4

L

3

2

3

5

7

8

9

10

11

12

Pos.1

Pos.5

P2

25±5

YYWW

MADE IN CHINA

35±2

13±2

Clear

LABEL DETAIL

NOTES:

1. 100% ELECTRICAL TEST.

2. PACKAGE: 1PCS/PE BAG.

3. 360°C SOLDERING.

4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.

PIN ASSIGNMENT :

P1

2

3

Pair 1

White(D-)

Green(D+)

Red(V BUS)

Black(Gnd)

Drain

Braid

Shell

P2

2

3

1

5

Shell

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

-

DWN

BOVEY LIU

28/JUN/01

CHK

BEVIN

28/JUN/01

APVD

MARK

28/JUN/01

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

CABLE ASSY, MINI USB B TYPE TO USB A TYPE

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=1496476

RESTRICTED TO

-

SCALE

N.T.S.

SHEET

1 of 1

REV

S

PART NO.

LENGTH(L)

CABLE

AWG

CABLE O.D.

(REF)

1496476-1

1000⁺⁰₋₃₀ MM

1P*28AWG+2C*26AWG

4.2 mm

1496476-2

1500⁺⁰₋₃₀ MM

1P*28AWG+2C*24AWG

4.5 mm

1496476-3

2000⁺⁰₋₃₀ MM

1P*28AWG+2C*24AWG

4.5 mm

1496476-4

3000⁺⁰₋₅₀ MM

1P*25AWG+2C*22AWG

5.2 mm

1496476-5

5000⁺⁰₋₅₀ MM

1P*25AWG+2C*20AWG

5.2 mm

1496476-6

305⁺⁰₋₃₀MM

1P*28AWG+2C*28AWG

3.5 mm

1

2

3

4

5

6

7

8

9

10

11

12

UL TAPE, W: 9MM, COLOR: BLACK

CONNECTOR,MINI USB B TYPE

CONNECTOR,MINI USB B TYPE

Heat Shrink Tubing 1.0MM BLACK

Copper Foil, W: 5.0MM

Heat Shrink Tubing, 1.5mm, Color: Black

PVC TUBE, ID: 1.5MM, COLOR: BLACK

Heat Shrink Tubing, 1.0mm, Color: Black

LABEL , 25*35mm.

Copper Foil, W: 10.0MM.

USB 2.0 Cable, 1P(Signal)+2C(Power)+Al/Mylar

+Drain+Braid, Color: Black.

Mini USB, B PLUG, SOLDER TYPE

Overmolded PVC,Color: Black(BK01).Shore A 80±5

USB A Type Solder Contacts: Gold Plated 30U"

Shell: Nickel Plated, Insulation: White

ITEM

12

11

10

9

8

7

6

5

4

3

2

1

1496476

1471-9 (3/11)

13APR2012 11:11am us022590 C:\A-WORK\REVISED\1496476_1-c.dwg