
7

6


8

C 2019 TE Connectivity. All Rights Reserved.


4805 (3/|3)





5




DETAIL A OPTIONAL CONSTRUCTIONS







4



THIS DRAWING IS A CONT DIMENSIONS: mm O F 2 F 3 F 4 F ANC MATERIAL NYLON 94V-0

3

		1						
	REVISIONS							
Ρ	LTR	DESCRIPTION	DATE	DWN	APVD			
	V 6	REDRAWN PER ECO-19-005708	03MAY2019	BKW	SF			

- 1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOCK $^{\mathsf{TM}}$ plug
- 2. RECOMMENDED PANEL THICKNESS 0.76 2.29.

3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH. \wedge

- 4 OPTIONAL FOR KEYING HOUSING IN PANEL.
- 5 CIRCUIT NUMBER 1 LOCATION.
- 6. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- A UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
- 9 TRADEMARK LOCATION: AMP OR TE

	CUSTOMER	RESTRICTED	NATURAL	350780-2
			BLACK	1 - 350780 - 9
			GRAY	1 - 350780 - 8
			BLUE	1 - 350780 - 6
			GREEN	1 - 350780 - 5
			YELLOW	1 - 350780 - 4
			ORANGE	1 - 350780 - 3
		OBSOLETE	RED	1 350780-2
			BROWN	1 - 350780 - 1
			NATURAL	350780-1
			COLOR	PART NUMBER
NTROLLED DOCUMENT.	DWN 03MAY2019 B. WEAVER снк 03MAY2019 S. FERNANDES		ETE TE	Connectivity
TOLERANCES UNLESS OTHERWISE SPECIFIED:) PLC ±- PLC ±-	APVD 03MAY2019 T. BENCHOFF PRODUCT SPEC	^{NAME} САР, 4 -	CIRCUIT, UNIVE	RSAL MATE-N-LOK
2 PLC ±0.13 3 PLC ±-	APPLICATION SPEC	-		
↓ PLC ±- ANGLES ±1°	-	SIZE CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH -	WEIGHT _	A 00779	<u> </u>	-
	CUSTOMER DRAWING		scale 4:1	ieet of revV6

В