



TOP VIEW



END VIEW



SIDE VIEW

SYMBOL	DIMENSIONS			
	MM		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	2.44	2.64	.096	.104
A1	0.10	0.29	.004	.011
b	0.30	0.44	.012	.017
c	0.23	0.32	.009	.013
D	15.20	15.55	.598	.612
E	7.40	7.60	.291	.299
H	10.10	10.51	.398	.414
L	0.51	1.02	.020	.040
e	0.80 BSC		.0315 BSC	
PKG CODE	A36-2, A36-3, A36-4, A36MK-4			

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
3. D & E DO NOT INCLUDE MOLD FLASH.
4. MOLD FLASH OR PROTRUSIONS NOT TO EXCEED 0.15mm (.006").
5. LEADS TO BE COPLANAR WITHIN 0.10mm (.004").
6. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbFREE (+) PKG. CODES.

-DRAWING NOT TO SCALE-

**MAXIM**

TITLE:  
PACKAGE OUTLINE,  
36L SSOP, 0.80 MM PITCH

APPROVAL  
RAMON DE LEON  
3/9/10

DOCUMENT CONTROL NO.  
21-0040

REV. 1/1  
F