


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16	A2	ADDED 5-0	08MAY08	KH JD

- 1. MAXIMUM CONNECTOR INSERTION LOSS IS 0.40dB PLUS CABLE ATTENUATION OF 0.70dB/km AT 1300nm. (SEE TABLE)
- 2. MINIMUM RETURN LOSS: 55dB
- 3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



0.44	50.00±0.50 [1968.5±19.7]	5-5492015-0
0.41	12.19±0.15 [480.0±5.9]	3-5492015-2
0.40	1.37±0.05 [53.9±2.0]	3-5492015-1
0.40	0.46±0.03 [18.1±1.0]	3-5492015-0
0.47	100.00±1.00 [3937.0±39.4]	2-5492015-9
0.44	60.00±0.60 [2362.2±23.6]	2-5492015-5
0.43	40.00±0.40 [1574.8±15.8]	2-5492015-2
0.42	30.00±0.30 [1181.1±11.8]	2-5492015-1
0.42	35.00±0.35 [1378.0±13.8]	2-5492015-0
0.40	4.00±0.08 [157.5±3.2]	1-5492015-9
0.41	25.00±0.30 [984.0±11.8]	1-5492015-6
0.41	9.00±0.15 [354.3±5.9]	1-5492015-4
0.41	8.00±0.15 [315.0±5.9]	1-5492015-3
0.40	6.00±0.08 [236.2±3.0]	1-5492015-2
0.40	1.50±0.05 [59.1±2.0]	1-5492015-1
0.40	0.75±0.03 [29.6±1.0]	1-5492015-0
0.40	0.30+0.05/-0.0 [11.8+2.0/-0]	5492015-9
0.40	7.00±0.08 [275.6±3.2]	5492015-8
0.41	20.00±0.30 [787.4±11.8]	5492015-7
0.41	15.00±0.15 [591.6±5.9]	5492015-6
0.41	10.00±0.15 [393.7±5.9]	5492015-5
0.40	5.00±0.08 [196.8±3.2]	5492015-4
0.40	3.00±0.05 [118.1±2.0]	5492015-3
0.40	2.00±0.05 [78.7±2.0]	5492015-2
0.40	1.00±0.05 [39.4±2.0]	5492015-1

MAX IL (dB)	L METERS [INCHES]	PART NUMBER
-------------	-------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. W. DAVIS 21OCT05	Tyco Electronics Corporation Harrisburg, PA 17105-3608
CHK J. DUNCAN 21OCT05	
APVD F. McCORKEL 21OCT05	NAME CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE 2.9mm OFNR CABLE, SC TO SC, RoHS
PRODUCT SPEC	
APPLICATION SPEC	
MATERIAL	WEIGHT
CUSTOMER DRAWING	

SIZE A2	CAGE CODE 00779	DRAWING NO 5492015	RESTRICTED TO
SCALE NTS	SHEET 1 of 1	REV A2	