



1) Fiberglass braided sleeve, 2) Red iron oxide flame protection

**Basic features**

<b>Scope of delivery</b>	Protective tube
<b>Short description</b>	Silicone-fiberglass tube
<b>Use</b>	for cable guard for weld protection

**Material**

<b>Material</b>	Glass fiber jacketed Silicone rubber, red
<b>Surface protection</b>	Iron oxide red silicone rubber

**Environmental conditions**

<b>Ambient temperature</b>	-55...260 °C
----------------------------	--------------

**Mechanical data**

<b>Dimension</b>	Ø 20.7 x 30480 mm
<b>Size</b>	1/2"

**Remarks**

GL German Lloyd certified at 800°C for 30 minutes, UL1441- certified, UL VW1-certified for flame resistance, SAE AS1072E- certified for fire protection shell on hoses, MSHA approval for fire protection on hoses in underground mines, DIN 54837/5510-2 railway certified for fire resistance, DIN 5659-2/5510-2 railway certified for low toxicity.