

4MT5
(CYJV CABLE ASSEMBLY)



Basic features

Approval/Conformity	EAC cULus WEEE
---------------------	----------------------

Electrical connection

Cable diameter D	3.5...5 mm
Connection	M8x1-Male, Straight, 4-pin, A-coded
Number of connectable contacts	4
System	Can be fabricated

Electrical data

Operating voltage U_b	60 VDC / 60 VAC
Rated current (40 °C)	4.0 A

Environmental conditions

Ambient temperature	-40...85 °C
Protection degree	IP67

Material

Material contact carrier	PA
Material contacts	Brass
Material cover nut	Brass
Material grip	PBT


Mechanical data

Connection cross-section	0.14...0.5 mm ²
Tightening torque pigtail	0.4 Nm
Type of wire mounting	Screw terminals

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings



PIN 1-4 usable