

**Basic features**

Approval/Conformity	EAC WEEE
---------------------	-------------

**Electrical connection**

Connection 1	M12x1-Male, 4-pin, A-coded
Connection 2	M8x1-Female, 3-pin, A-coded
Connection 3	M8x1-Female, 3-pin, A-coded
Number of pins	4/3/3

**Electrical data**

Operating voltage Ub	30 VDC / 30 VAC
Rated current (40 °C)	4.0 A

**Environmental conditions**

Ambient temperature	-25...85 °C
Protection degree	IP68

**Material**

Material contact carrier	PUR
Material contacts	Brass/Bronze/Bronze
Material cover nut	Die-cast zinc/Die-cast zinc/Die-cast zinc
Material grip	PUR


**Mechanical data**

Tightening torque pigtail	0.6 Nm/0.4 Nm/0.4 Nm
---------------------------	----------------------

**Remarks**

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

**Connector Drawings**



## Wiring Diagrams

