

Basic features

Approval/Conformity	EAC WEEE
---------------------	-------------

Display/Operation

Power indicator	no/no
-----------------	-------

Electrical connection

Connection 1	M12x1-Female, angled, 4-pin, D-coded
Connection 2	RJ45-Female, straight, 4-pin
Connector 01, version	right-angle
Connector 02, version	Straight
Number of pins	4/4

Electrical data

Operating voltage U_b	60 VDC / 60 VAC
Rated current (40 °C)	0.5 A

Environmental conditions

Ambient temperature	-20...80 °C
Protection degree	IP20



Material

Material contact carrier	PUR
Material contacts	Brass/Brass
Material grip	PUR


Mechanical data

Mounting	M16x1.5
----------	---------

Connector Drawings



Wiring Diagrams



- 1) Shield on cover nut
- 2) Shield on housing