



### Basic features

<b>Approval/Conformity</b>	cURus EAC WEEE
----------------------------	----------------------

### Electrical connection

<b>Cable diameter D</b>	4...6 mm
<b>Connection</b>	M12x1-Female, right-angle, 5-pin, A-coded
<b>Number of connectable contacts</b>	5
<b>System</b>	Can be fabricated

### Electrical data

<b>Operating voltage <math>U_b</math></b>	125 VDC / 125 VAC
<b>Rated current (40 °C)</b>	4.0 A

### Environmental conditions

<b>Ambient temperature</b>	-40...85 °C
<b>Protection degree</b>	IP67

### Material

<b>Material contact carrier</b>	PA
<b>Material contacts</b>	Brass
<b>Material cover nut</b>	Die-cast zinc
<b>Material grip</b>	PA

### Mechanical data

<b>Connection cross-section</b>	0.14...0.75 mm <sup>2</sup>
<b>Tightening torque pigtail</b>	0.6 Nm
<b>Type of wire mounting</b>	Screw terminals

### Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

### Connector Drawings

