

### Basic features

Approval/Conformity	EAC WEEE
---------------------	-------------

### Electrical connection

Conductor cross-section	0.25 mm <sup>2</sup>
Connection	M12x1-Female, Straight, 4-pin, A-coded
Number of conductors	4

### Electrical data

Operating voltage U <sub>b</sub>	250 VDC / 250 VAC
Rated current (40 °C)	4.0 A

### Environmental conditions

Ambient temperature	-40...85 °C
Protection degree	IP68

### Material

Conductor insulation material	TPE
Housing material	Die-cast zinc, nickel plated
Housing material, surface protection	nickel plated
Material contact carrier	PA
Material contacts	Bronze


### Mechanical data

Lead length L	0.50 m
Mounting	M16x1.5

### Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.  
 Nut M16 included in scope of delivery

## Connector Drawings



- PIN 1: brown
- PIN 2: white
- PIN 3: blue
- PIN 4: black

## Wiring Diagrams

