

Basic features

Approval/Conformity	EAC WEEE
---------------------	-------------

Electrical connection

Conductor cross-section	0.25 mm ²
Connection	M12x1-Male, Straight, 5-pin, A-coded
Number of conductors	5

Electrical data

Operating voltage U_b	60 VDC / 60 VAC
Rated current (40 °C)	4.0 A

Environmental conditions

Ambient temperature	-40...85 °C
Protection degree	IP68

Material

Conductor insulation material	TPE
Housing material	Die-cast zinc, nickel plated
Housing material, surface protection	nickel plated
Material contact carrier	PA
Material contacts	Brass


Mechanical data

Lead length L	2.00 m
Mounting	M16x1.5

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.
 Nut M16 included in scope of delivery

Connector Drawings



- PIN 1: brown
- PIN 2: white
- PIN 3: blue
- PIN 4: black
- PIN 5: gray

Wiring Diagrams

