



Basic features

Approval/Conformity	CE WEEE
Function	Analog value display
Short description	Digital panel meter

Display/Operation

Keypad	Membrane keypad
Setting	Input signal selection Decimal point Tare Scaling

Electrical data

Input resistance	Voltage ≥ 50 kOhm, current 10 Ohm
Rated input current	65 mA

Environmental conditions

Ambient temperature	0...60 °C
IP rating IEC 60529 (connector)	IP20
Relative humidity	$\leq 80\%$
Storage temperature	-20...70 °C

Material

Housing material	Plastic
------------------	---------

Mechanical data

Dimension	72 x 48 x 96 mm
IP rating (front housing)	IP54
Panel cut-out	45 x 92 mm

Output/Interface

Analog inputs	Analog, voltage/analog, current (0...10 V/0...20 mA/4...20 mA)
Cycle time min.	200 ms
Interface	2x analog, voltage/analog, current

Range/Distance

Resolution	≤ 12 bits
------------	----------------

Wiring Diagrams

