



### Basic features

<b>Application</b>	Pneumatic cylinder with integrated groove Mannesmann-Rexroth green Series
<b>Basic standard</b>	Dimension tolerances: DIN ISO 2768 m
<b>Principle of operation</b>	BMF mounting bracket
<b>Scope of delivery</b>	Fastening screw Mounting bracket Offset screwdriver
<b>Use</b>	for magnetic sensors BMF 305

### Environmental conditions

<b>Ambient temperature</b>	-40...85 °C
----------------------------	-------------

### Material

<b>Material</b>	Aluminum
<b>Surface protection</b>	Anodized

### Mechanical data

<b>Mounting, holder</b>	Threaded pin ISO 4027 M3x4-A2 Offset screwdriver ISO 2936 1.5
<b>Sensor attachment</b>	Cylinder head screw DIN 7984 M3x5-A2 offset screwdriver ISO 2936 2.0
<b>Size</b>	L-slot
<b>Tightening torque</b>	1.5 Nm
<b>Tightening torque clamping screw</b>	1.5 Nm

## Help Views

