

Mechanical data

| | |
|-----------|--------------------|
| Dimension | 30 x 24 x 129.5 mm |
| Mounting | 2-hole screw mount |


Output/Interface

| | |
|---------------------------|-------------------|
| Cycle time min. | 2.5 ms |
| Digital inputs | 16x PNP, Type 2 |
| IO-Link version | 1 |
| Interface | IO-Link 1.0 |
| Process data IN | 4 bytes |
| Process data cycle min. | 10 ms |
| Single-channel monitoring | yes |
| Transfer rate | COM2 (38.4 kBaud) |

Remarks

See short guide

Connector Drawings




IO-Link

PIN 1: +24V

PIN 2: n.c.

PIN 3: GND, reference potential

PIN 4: IO-Link



Input Ports

PIN 1: +24V

PIN 2: Input

PIN 3: 0V

PIN 4: Input