



## Output/Interface

Cycle time min.	3.5 ms
Digital inputs	16x PNP, Type 3
Digital outputs	16x PNP
IO-Link version	1.1

Interface	IO-Link 1.1
Process data IN	2 bytes
Process data OUT	2 bytes
Process data cycle min.	3.5 ms
Transfer rate	COM2 (38.4 kBaud)


## Remarks

See short guide

For more information about MTTF and B10d see MTTF / B10d Certificate


Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Connector Drawings



IO-Link

- PIN 1: +24V, 1.5A Controller
- PIN 2: +24V, 1.6A actuators
- PIN 3: GND, reference potential
- PIN 4: C/Q, IO-Link DC-Channel



Digital In-/Output Port

- PIN 1: +24V, 0.2A
- PIN 2: Input/Output 2
- PIN 3: 0V / GND
- PIN 4: Input/Output 1
- PIN 5: Function ground