



Basic features

Approval/Conformity	CE EAC WEEE
Scope of delivery	Short guide

Display/Operation

Actuator supply UA, indicator	Green LED
IO-Link communication indicator	Green LED
Module supply indicator	Green LED
Sensor supply US indicator	Green LED
Switching function display	LED yellow

Electrical connection

Connection (COM 1)	Pluggable without terminals, 4-pin
Connection (supply voltage IN)	Pluggable without terminals
Connection slots	Pluggable without terminals

Electrical data

Burst	3A/4B
Configurable inputs/outputs	yes
Current consumption without load, max.	80 mA
IO-Link function	Device
IO-Link ports, number	1
Operating voltage Ub	18...30.2 VDC
Rated operating voltage Ue DC	24 V
Switching current	16x 350 mA

Environmental conditions

Ambient temperature	-20...50 °C
Protection degree	IP20
Storage temperature	-25...70 °C

Material

Housing material	PA 6.6, UL94V-0
Housing shield	no

I/O modules

BNI IOL-310-000-K025-001

Order Code: BNI007R

BALLUFF

Mechanical data

Dimension	79 x 33.6 x 84 mm
Mounting	DIN rail mount

Output/Interface

Cycle time min.	3 ms
Digital inputs	16x PNP, Type 2
Digital outputs	16x PNP
IO-Link version	1
Interface	IO-Link 1.0
Process data IN	2 bytes
Process data OUT	2 bytes
Process data cycle min.	12 ms
Transfer rate	COM2 (38.4 kBaud)

Remarks

Associated screw clamps (BAM01ZH) or spring clamps (BAM01ZK) must be ordered separately.
See short guide