



- 注記
- △ \square から2mmの範囲で測定
 - 嵌合相手ハウジング型 175109, 175110, 175111
 - 推奨取付ねじ: JIS B1115, B1122 タップピンねじ, なべ2種
 呼び径3, 長さ6mm以下 (勝付トルク: 0.4N-m(4kg-cm)以下)
 - 適用製品規格番号: 108-5280
 - △ コンタクト仕上識別マーク


- NOTES
- MUST BE KEPT BETWEEN \square AND 2
 - THE MATING PLUG HSG. PART NUMBER: 175109, 175110, 175111
 - RECOMMENDED MOUNTING SCREW: 3mm DIA, 6mm LENGTH MAX.
 PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
 (TIGHTENING TORQUE: 0.4N-m(4Kg-cm) MAX.)
 - APPLICABLE PRODUCT SPEC NO. 108-5280
 - △ MARKING FOR DISCERNMENT OF THE CONTACT FINISH



断面 A-A
 (SECT. A-A)



断面 B-B
 (SECT. B-B)



SEE CUSTOMER DRAWING 9-176122-6		9-176122-6	
2	PRE-TIN × 56 TIN-LEAD SELECTIVE GOLD × 8	-	57~64
0	PRE-TIN	-	ORANGE
0	PRE-TIN	-	GRAY
1	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	GRAY
MARKING マーキング	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	POWER CIRCUIT NO パワー回路
	CONTACT FINISH コンタクト仕上		SIGNAL CIRCUIT NO シグナル回路
GOLD PLATED CIRCUIT NO 金めっき回路番号		COLOR 色	PART NUMBER 製品型番
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: 単位: 寸 mm		DRAWN M. KADOSAKI CHK T. SHINOHARA	12OCT05 12OCT05
TOLERANCES UNLESS OTHERWISE SPECIFIED 公差 0. PLC ± 1. PLC ± 2. PLC ± 3. PLC ± 4. PLC ± ANGLES ±		APPROV K. BETSUJI	12OCT05 NAME 5名
GENERAL TOLERANCE 0<< 10 ±0.2 10<< 30 ±0.25 30<< 100 ±0.3 ANGLES ±3°		TE Connectivity 64POS. CAP HOUSING ASSY .040/.070 SERIES HYBRID I/O CONN.	
MATERIAL HOUSING: PBT CONTACT: BRASS		SIZE A1 CODE CODE 00779 DRAWING NO 176122 RESTRICTED TO -	
FINISH 仕上 SEE TABLE		WEIGHT CUSTOMER DRAWING SCALE 2:1 SHEET 1 of 1 REV G3	