


4

3




2

1


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J		B1		REVISED	30SEP2010	T.M
		C		ITEM ADDITION	19APR2011	M.M N.Y



- 1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY
- 2. FINISH(ALL OVER): NICKEL PLATED 1.27μmMIN
- 3. FINISH(CONTACT AREA): GOLD PLATED 0.38μmMIN AFTER 2.
- 4. FINISH(CONTACT TAIL): TIN PLATED 2μmMIN AFTER 2.



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1



20P: 1-1827873-0

20	X	9	18.0	21.0	22.6	1-1827873-0
10	Y	4	8.0	11.0	12.6	2-1827873-5
10	X	4	8.0	11.0	12.6	1-1827873-5
POS	KEY	n	A	B	C	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
1

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.3, ±3°

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH
2 3 4

DWN T.KUDO 17JAN2005

CHK D.MITSUGI 31AUG2005

APVD D.MITSUGI 31AUG2005

PRODUCT SPEC 108-78268

APPLICATION SPEC 114-5377

WEIGHT

CUSTOMER DRAWING

TE Connectivity




NAME
DYNAMIC D1100D 2.0mmPITCH
HDR ASSY, H-TYPE
4-20POS

SIZE A3 CAGE CODE 00779 DRAWING NO C-1827873


RESTRICTED TO

SCALE 4:1 SHEET 1 OF 2 REV C


LOC	DIST	REVISIONS				
J		P	LTR	DESCRIPTION	DATE	APVD
				SEE SHEET 1		



10P(Y):2-1827873-5



10P(X):1-1827873-5

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KUDO	17JAN2005	 TE Connectivity									
DIMENSIONS: mm		CHK D.MITSUGI	31AUG2005	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY, H-TYPE 4-20POS									
		APVD D.MITSUGI	31AUG2005										
		PRODUCT SPEC 108-78268		SIZE A3		CAGE CODE 00779		DRAWING NO C-1827873		RESTRICTED TO -			
APPLICATION SPEC 114-5377													
MATERIAL -		FINISH -		WEIGHT -		CUSTOMER DRAWING							
						SCALE 4:1		SHEET 2		OF 2		REV C	