

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL INTERNATIONAL RIGHTS RESERVED.

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

LOC
JDIST
—

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD






E

REVISED

26AUG10

T.T


T.M


TRADE MARK
ID MARK No.1断面 B-B
SECT.断面 C-C
SECT.

SERIES MARK

NOTE

1. Application REC-HSG is applied to the product of 2.5mm PITCH or more of DYNAMIC D1000SERIES. 2.0mmPITCH cannot be used

0.5tタブにかん合
MATE WITH 0.5t TAB断面 A-A
SECT.

AWG#28~#22 0.08~0.38mm ²	φ1.08~φ1.9	COPPER ALLOY,FINISH:CONTACT AREA Au 0.38μm MIN,OVER Ni 1.27μm MIN 材料:銅合金,下地:Niめっき1.27μm以上,接点部:金めっき0.38μm以上	1827571-2
WIRE RANGE 導体断面積	INSULATION DIA 被覆外径	MATERIAL 材料	PART No. 型番
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KUDO 04MAR2005	 Tyco Electronics Corporation Kawasaki, Japan
		CHK D.MITSUGI 04MAR2005	
		APVD D.MITSUGI 04MAR2005	
DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	PRODUCT SPEC 製品規格 108-78268	NAME 名称 DYNMIC D1000 SERIES REC CONTACT L TYPE REEL
	0 PLC ± 0.3 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± 3deg	APPLICATION SPEC 取付適用規格 114-5377	
MATERIAL 材料	FINISH 仕上	WEIGHT —	SIZE A3
		CUSTOMER DRAWING	CAGE CODE 00779
		DRAWING NO 番号 C-1827571	RESTRICTED TO —
		SCALE 尺度 10:1	SHEET 1 OF 1
		REV E	