


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES TDG1026-4R-OD1 AT REV A	11/13/14	D. CASTRO
.	.	.	.
.	.	.	.
.	.	.	.



WIRE MAP	
"J1"	"J2"
2	5
3	4
4	3
5	2

NOTES:

- CROSS WIRED.
- UL94V-0 FLAMMABILITY RATING.
- JACK PIN PLATING: 15 MICROINCHES GOLD OVER NICKEL.
- COMPONENT SHALL BE TESTED FOR CONTINUITY.
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY TJC	10/3/01		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY DFP	10/4/01	CATEGORY TELECOM/MODULAR	
	APPROVED BY RC	10/9/01	PRODUCT DESCRIPTION MODULAR COUPLER 6X4 CROSSED	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. TDG1026-4R	REV. A
			SCALE: NONE	CAD FILE: TDG1026-4R.SLDDRW
				SHEET 1 OF 1