









TRADE MARK



NOTE



- MATED WITH : 104085-0400, 104085-0410 , 101085-0420
- MATERIALS
 - HEADER : LCP(E130I), GLASS FILLED, UL94V-0, HALOGEN FREE, COLOR OF NATURAL
 - FITTING NAIL : PHOSPHOR BRONZE, 0.2mm THICKNESS
 - CONTACT TERMINAL : POSPHOR BRONZE, 0.25mm THICKNESS
- FINISHES
 - FITTING NAIL : PURE-TIN PLATING ON OVERALL. THICKNESS 3.0μm-5.0μm UNDER PLATING Ni OVERALL. THICKNESS 1.25μm-3.75μm
 - CONTACT TERMINAL : PURE-TIN PLATING ON OVERALL. THICKNESS 3.0μm-5.0μm UNDER PLATING Ni OVERALL. THICKNESS 1.25μm-3.75μm
- COPLANALITY OF SOLDER TAILS (PEAK TEMP. : 260°C), BEFORE & AFTER REFLOW : 0.08MAX

NEW RELEASED EC NO: KOR2011-0057 DRWN:CBCHIN 2010/12/02 CHKD:SH.CHU 2010/12/02 APPR:YUNSI/KKIM 2010/12/02	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)
	▽=0	
	▽=0	
	▽=0	

mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± ---
2 PLACES ± 0.20	± ---
1 PLACE ± 0.25	± ---
ANGULAR ± ---°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	



DRAWN BY	DATE	TITLE
JB.JIN	2010/07/08	
CHECKED BY	DATE	
SH.CHU	2010/07/08	
APPROVED BY	DATE	
YS00.KIM	2010/07/08	
MATERIAL NO.		
1040860410		

ORDER NUMBER	104086-0410
DESIGN UNITS	METRIC
THIRD ANGLE PROJECTION	
1.25 W-T-B CONN. HEADER ASS'Y-4P	
MOLEX INCORPORATED	
DOCUMENT NO.	SD-104086-001
SHEET NO.	1 OF 01




SECTION A-A


PULL OUT DIRECTION



SECTION B-B




PLASTIC BOBBIN




NOTES

1. QUANTITY OF CONNECTORS : 2,000 PCS/REEL

2. LEAD LENGTH



3. PEELING OFF FORCE OF COVER TAPE : 0.1N~0.59N(10.2GF~60GF)
(PEELING DIRECTION AS SHOW IN FOLLOW FIG.)
PEELING OFF SPEED : 300mm/Min.(Ref.)



4. FLASH IN ANY PORTION SHOULD BE LESS THAN 0.20mm MAX.
5. UNLESS OTHERWISE SPECIFIED INNER R0.2 MAX
6. DRAFT ANGLE 3°MAX

3	PLASTIC BOBBIN	HI P.S	WHITE
2	COVER TAPE	PET ANTISTATIC	21.3m
1	CARRIER (EMBOSSD) TAPE	PET ANTISTATIC	
NO.	DESCRIPTION	MATERIAL	REMARK

ORDER NO. 104086-0410

DESIGN UNITS METRIC THIRD ANGLE PROJECTION

1.25 W-T-B CONN
HEADER ASS'Y-4P
EMBOSSD PACKAGE

MOLEX INCORPORATED

DOCUMENT NO. SD-104086-002 SHEET NO. 1 OF 01

REV	DESCRIPTION	QUALITY SYMBOLS
A	NEW RELEASED EC NO: KOR2011-0057 DRWN:CBCHIN 2010/12/02 CHKD:SH. CHU 2010/12/02 APPR:YUNSIKIM 2010/12/02	

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.25	± ---
1 PLACE	± 0.25	± ---
ANGULAR ± 3 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
JB. JIN	2010/07/09
CHECKED BY	DATE
SH. CHU	2010/07/09
APPROVED BY	DATE
YS00.KIM	2010/07/09
MATERIAL NO. 1040860410	
SIZE A3	

SCALE 4:1	TITLE
	1.25 W-T-B CONN HEADER ASS'Y-4P EMBOSSD PACKAGE
	MOLEX INCORPORATED
	DOCUMENT NO. SD-104086-002 SHEET NO. 1 OF 01