


LC ADAPTER P/N	COLOR	SPLIT SLEEVE MATERIAL
86127-1300	BLUE	Zr
86127-1320 (SEE NOTE 2)		
86127-0310	BEIGE	Ph. Bronze
86127-1350	GREEN	Zr
86127-1500	BLUE/METAL DOOR	Zr
86127-0510	BEIGE/METAL DOOR	Ph. Bronze
86127-1550	GREEN/METAL DOOR	Zr



NOTES:

- DUST CAPS ARE NOT SHOWN, BUT INCLUDED.
- FOR P/N 86127-1320 LASER WARNING LABEL IS SUPPLIED UNATTACHED AND SHALL BE INSTALLED BY CUSTOMER.

ENTER DESCRIPTION EC NO: MF2005-0160 DRAWN: IGLUMIN CHKD: APPR: IGLUMIN 2004/09/09 2004/09/09 2004/09/09	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION																		
		<table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± .005</td> <td>± .0004</td> </tr> <tr> <td>3 PLACES</td> <td>± .004</td> <td>± .0003</td> </tr> <tr> <td>2 PLACES</td> <td>± .003</td> <td>± .0002</td> </tr> <tr> <td>1 PLACE</td> <td>± .002</td> <td>± .0001</td> </tr> <tr> <td colspan="3">ANGULAR ±1/2°</td> </tr> </tbody> </table>		mm	INCH	4 PLACES	± .005	± .0004	3 PLACES	± .004	± .0003	2 PLACES	± .003	± .0002	1 PLACE	± .002	± .0001	ANGULAR ±1/2°			IN/MM	4:1	INCH	
		mm	INCH																					
	4 PLACES	± .005	± .0004																					
3 PLACES	± .004	± .0003																						
2 PLACES	± .003	± .0002																						
1 PLACE	± .002	± .0001																						
ANGULAR ±1/2°																								
			DRAWN BY	DATE	TITLE																			
			BKIM	11.29.99	LC DUPLEX ADAPTER W/SHUTTERS (STANDARD FLANGE/SC FOOT PRINT)																			
			CHECKED BY	DATE																				
			DSZILAGY	12.20.99																				
			APPROVED BY	DATE																				
			SMIGO	12.21.99																				
			MATERIAL NO.	DOCUMENT NO.		SHEET NO.																		
			SEE TABLE	86127-XXXOCD		1 OF 1																		
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																					