




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	05/24/2022	GUTTADAURO



DETAIL A





DETAIL B



DETAIL C

NOTES:

- VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 2000V/1 SECOND
CONDUCTOR RESISTANCE: ≤26.0 Ω/1000 METERS
VOLTAGE RATING: AC 300V
- CABLE MARKING:
CCC A133679 60227 IEC 52(RVV) 300/300V 2X0.75mm²
- OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
- CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ±1° .XXX = ±.005 [.13]	APPROVALS	DATE	 an INFINITI® brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY AKRESOWSK	04/27/2022		
THIRD-ANGLE PROJECTION 	CHECKED BY DGUST	04/27/2022	CATEGORY POWER PRODUCTS	
	APPROVED BY GUTTADAURO	04/27/2022	PRODUCT DESCRIPTION CABLE ASSY, INTL PWR, TYPE A TO C7, 2.5A, 2M	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	CAGE CODE 43321
	COLOR VARIATIONS MAY OCCUR		ITEM NO. IPCAC7-2.5A-2M	REV. A
			SCALE: NONE	CAD FILE: IPCAC7-2.5A-2M.SLDDRW
				SHEET 1 OF 1