



Basic features

Principle of operation	BTL magnet, rod
Scope of delivery	Spacer Position sensor

Environmental conditions

Ambient temperature	-40...100 °C
Storage temperature	-40...100 °C

Material

Housing material	PA, PO 60, GF
-------------------------	---------------

Mechanical data

Application weight	10.00 g
Dimension	Ø 25 x 8 mm
Inside diameter	12.0 mm
Mounting part	Through-hole 3.2 mm (2x)
Pressure rating max.	600 bar