



### Basic features

<b>Scope of delivery</b>	Protective cap Nut M22x1.5 (2x)
<b>Short description</b>	Padded Proxy holder
<b>Use</b>	For M12 sensors for inductive sensors BES for inductive sensors BES M12

### Environmental conditions

<b>Ambient temperature</b>	-45...85 °C
----------------------------	-------------

### Material

<b>Housing material</b>	POM, black, Anodized Aluminum, black anodized
<b>Material</b>	Aluminum
<b>Surface protection</b>	Anodized

### Mechanical data

<b>Clamping system</b>	Threads
<b>Diameter 2</b>	12.00 mm
<b>Dimension</b>	Ø 22 x 21 mm
<b>Life expectancy mechanical</b>	2 mil. switching operations
<b>Mounting part</b>	M22x1.5
<b>Size</b>	M12x1
<b>Spring deflection</b>	15 mm
<b>Spring force</b>	4.04 N
<b>Stop force F max.</b>	7.79 N
<b>Tightening torque max.</b>	15 Nm