



Basic features

Principle of operation BTL magnet, rod

Environmental conditions

Ambient temperature -40...100 °C
Storage temperature -40...100 °C

Material

Housing material PA, PO 60, GF

Mechanical data

Application weight 10.00 g
Dimension Ø 32 x 8 mm
Inside diameter 13.0 mm
Mounting part Through-hole 4.3 mm (2x)
Pressure rating max. 600 bar