

Basic features

Approval/Conformity	CE UKCA cULus WEEE
Scope of delivery	Machine light Ø45 mm
Version	Machine light

Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes

Electrical data

Current draw max.	1250 mA
Protection class	III
Rated operating voltage Ue DC	24 V

Environmental conditions

Ambient temperature	-20...40 °C
IP rating	IP67

Material

Material	Aluminium Anodized Borosilicate crown glass
----------	--

Mechanical data

Dimension	Ø 45 x 1000 mm
-----------	----------------


Optical features

Beam angle	120 °
Color temperature	5000 K
Illumination area	960 x 42 mm
LED group per IEC 62471	Exempt Group
Light intensity	4500 lm
Light type	LED white light diffuse

Remarks

For additional information, refer to user's guide.
Suitable for continuous operation
Order accessories separately.
Install the device so that no direct view of the light source is possible even during operation.

Connector Drawings



PIN 1: +24V

PIN 2: not used

PIN 3: 0 V, DC

PIN 4: not used