



## Basic features

<b>Scope of delivery</b>	Mounting block Nut ISO 4032-M3 (2x) Screw ISO 4762-M3x8 (2x)
<b>Short description</b>	Fixed stop
<b>Use</b>	for inductive sensors $\varnothing 4$ for inductive sensors BES M8

## Environmental conditions

<b>Ambient temperature</b>	-25...100 °C
----------------------------	--------------

## Remarks

Switching point between the proximity switch and trigger pin can be set wherever needed.

## Material

<b>Material</b>	Aluminum
<b>Surface protection</b>	anodized, red

## Mechanical data

<b>Clamping system</b>	Threads
<b>Dimension</b>	31.8 x 12 x 20 mm
<b>Mounting part</b>	Clamps
<b>Tightening torque</b>	1.5 Nm
<b>Tightening torque max.</b>	1.5 Nm