



Basic features

Scope of delivery	Protective nut
Short description	Protective cap
Trademark	Global
Use	For M30 sensors

Environmental conditions

Ambient temperature	-200...250 °C
----------------------------	---------------

Material

Housing material	PTFE
-------------------------	------

Mechanical data

Dimension	Ø 41.3 x 73.4 mm
Inside diameter	30.00 mm
Installation	for flush mounting
Mounting part	Threads
Pressure rating max.	14 bar
Pressure rating, note	when properly installed
Size	M30x1.5
Tightening torque	2 Nm