



Basic features

Principle of operation BTL magnet, rod

Environmental conditions

Ambient temperature -40...60 °C
Storage temperature -40...85 °C

Material

Housing material PA 6, Ferrite

Mechanical data

Application weight 2.00 g
Dimension Ø 17.2 x 5 mm
Inside diameter 14.0 mm
Mounting part Clamped
Pressure rating max. 250 bar

Remarks

The position magnet BAM013H with a width of 5 mm is smaller compared to the standard position magnets (e.g. BAM013L) with 8 mm width. Please consider that the indicated position of the BAM013H is therefore 1,5 mm (50% of the difference between 5 and 8 mm width) lower compared to our standard magnets.