



Basic features

Principle of operation BTL magnet, rod

Environmental conditions

Ambient temperature -40...100 °C
Storage temperature -40...100 °C

Material

Housing material PA 6.6, GF30

Mechanical data

Application weight 16.00 g
Dimension Ø 37 x 8 mm
Inside diameter 18.0 mm
Mounting part Through-hole 4.3 mm (4x)
Pressure rating max. 250 bar