



**Basic features**

<b>Scope of delivery</b>	Protective cap Nut M30x1.5 (2x)
<b>Short description</b>	Padded Proxy holder
<b>Use</b>	For M18 sensors for inductive sensors BES for inductive sensors BES M18

**Environmental conditions**

<b>Ambient temperature</b>	-45...85 °C
----------------------------	-------------

**Material**

<b>Housing material</b>	POM, black, Anodized Aluminum, black anodized
<b>Material</b>	Aluminum
<b>Surface protection</b>	Anodized

**Mechanical data**

<b>Clamping system</b>	Threads
<b>Diameter 2</b>	18.00 mm
<b>Dimension</b>	Ø 30 x 29.7 mm
<b>Life expectancy mechanical</b>	2 mil. switching operations
<b>Mounting part</b>	M30x1.5
<b>Size</b>	M18x1
<b>Spring deflection</b>	15 mm
<b>Spring force</b>	5.56 N
<b>Stop force F max.</b>	10.49 N
<b>Tightening torque max.</b>	40 Nm