



Basic features

Approval/Conformity	CE WEEE
----------------------------	------------

Electrical connection

Cable diameter D	6...8 mm
Connection	M16x0.75-Female, angled, 8-pin
Contact shield	Shield ring
Number of connectable contacts	8
System	Can be fabricated

Electrical data

Operating voltage U_b	60 VDC / 60 VAC
Rated current (40 °C)	5.0 A

Environmental conditions

Ambient temperature	-30...95 °C
IP rating	IP67

Material

Material contact carrier	PBT
Material contacts	Bronze
Material cover nut	Brass
Material grip	Die-cast zinc

Mechanical data

Connection cross-section	0.14...0.75 mm ²
Type of wire mounting	Solder connections

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings

