

1) Hex nut, 2) O-ring



Basic features

Application	Panel connector
Approval/Conformity	cULus WEEE

Electrical connection

Conductor cross-section	22 AWG
Connection	M12x1-Female, straight, 4-pin, A-coded
Number of conductors	4

Electrical data

Operating voltage U_b	300 VDC / 300 VAC
Rated current (40 °C)	4.0 A

Environmental conditions

Ambient temperature	-40...105 °C
IP rating	IP67

Interface

Switching output	Complementary
-------------------------	---------------

Material

Conductor insulation material	PVC
Material contacts	Copper alloy
Material cover nut	Brass nickel-plated


Mechanical data

Lead length L	2.00 m
Mounting part	1/4"-18 NPT
Tightening torque pigtail	0.6 Nm

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings



PIN 1: brown
PIN 2: white
PIN 3: blue
PIN 4: black

Wiring Diagrams

