

## Basic features

**Approval/Conformity** WEEE

## Electrical connection

<b>Connection 1</b>	A, DIN-0°/180°-Valve connector, angled, 4-pin
<b>Connection 2</b>	M12x1-Male, straight, 3-pin, A-coded
<b>Connector 01, version</b>	angled
<b>Connector 02, version</b>	straight
<b>Number of pins</b>	4/3
<b>System</b>	Molded

## Electrical data

<b>Operating voltage <math>U_b</math></b>	24 VDC / 24 VAC
<b>Rated current (40 °C)</b>	4.0 A
<b>Suppressor</b>	Suppressor diode

## Environmental conditions

<b>Ambient temperature</b>	-25...80 °C
<b>IP rating</b>	IP67


## Material

<b>Material contact carrier</b>	PBT/PA
<b>Material contacts</b>	Brass/Brass
<b>Material grip</b>	TPU
<b>Material locking screw</b>	Steel

## Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Connector Drawings



## Wiring Diagrams

