



## Interface

<b>Cycle time min.</b>	2.5 ms
<b>Digital inputs</b>	16x PNP, Type 2
<b>IO-Link version</b>	1
<b>Interface</b>	IO-Link 1.0
<b>Process data IN</b>	4 bytes
<b>Process data cycle min.</b>	10 ms
<b>Single-channel monitoring</b>	yes
<b>Transfer rate</b>	COM2 (38.4 kBaud)

## Material

<b>Gasket, material</b>	FKM 75
<b>Housing material</b>	PBT, GF
<b>Housing shield</b>	no


## Mechanical data

<b>Dimension</b>	30 x 24 x 129.5 mm
<b>Mounting part</b>	2-hole screw mount

## Remarks

See short guide

## Connector Drawings




IO-Link

PIN 1: +24V

PIN 2: not used

PIN 3: GND, reference potential

PIN 4: IO-Link



Input Ports

PIN 1: +24V

PIN 2: Input

PIN 3: 0V

PIN 4: Input