



Basic features

Approval/Conformity	CE UKCA WEEE
Scope of delivery	Short guide

Display/Operation

Actuator supply UA, indicator	Green LED
IO-Link communication indicator	Green LED
Module supply indicator	Green LED
Sensor supply US indicator	Green LED
Switching function display	LED yellow

Electrical connection

Connection (COM 1)	Pluggable without terminals, 4-pin
Connection (supply voltage IN)	Pluggable without terminals
Connection slots	Pluggable without terminals

Electrical data

Configurable inputs/outputs	yes
Current consumption without load, max.	80 mA
Current sum UA, actuator	1.6 A
Current sum US, sensor	1.0 A
IO-Link function	Device
IO-Link ports, number	1
Operating voltage Ub	18...30.2 VDC
Rated operating voltage Ue DC	24 V
Switching current	8x 350 mA

Environmental conditions

Ambient temperature	-20...50 °C
IP rating	IP20
Storage temperature	-25...70 °C

IO-Link

IO-Link Profil IDs	N/A
--------------------	-----

I/O modules
BNI IOL-309-000-K024-001
Order Code: BNI007P

BALLUFF

Interface

Cycle time min.	3 ms
Digital inputs	8x PNP, Type 2
Digital outputs	8x PNP
IO-Link version	1
Interface	IO-Link 1.0
Process data IN	1 byte
Process data OUT	1 byte
Process data cycle min.	3.0 ms

Transfer rate

COM2 (38.4 kBaud)

Material

Housing material	PA 6.6, UL94V-0
Housing shield	no

Mechanical data

Dimension	48.6 x 33.6 x 84 mm
Mounting part	DIN rail mount

Remarks

Associated screw clamps (BAM01ZF) or spring clamps (BAM01ZJ) must be ordered separately.
See short guide