



1) Reference point, 2) Designation for upper side

Basic features

Principle of operation BTL magnet, float

Environmental conditions

Ambient temperature -20...120 °C
 Storage temperature -20...120 °C

Material

Housing material 1.4404 stainless steel

Mechanical data

Application weight 34.00 g
 Dimension Ø 50.90 mm/Ø 13.0 mm x 52.00 mm
 Immersion depth at $\rho = 0.7 \text{ g/cm}^3$ approx. 40 mm
 Immersion depth at $\rho = 1 \text{ g/cm}^3$ 26 mm
 Inside diameter 13.0 mm
 Pressure rating max. 40 bar