



1) Designation for upper side

Basic features

Principle of operation	BTL magnet, float
Scope of delivery	Cotter pin User manual Floats

Environmental conditions

Ambient temperature	-20...130 °C
Storage temperature	-20...120 °C

Material

Housing material	1.4404 stainless steel
------------------	------------------------

Mechanical data

Application weight	30 g
Dimension	Ø 31 mm/Ø 11.7 mm x 69 mm
Immersion depth at $\rho = 1 \text{ g/cm}^3$	53.4 mm
Inside diameter	11.7 mm
Pressure rating max.	4 bar