





– CONTACT IDENTIFICATION
LETTER "C" (LOCATED
IN THIS AREA)

- HOUSING
(SEE TABLE
FOR PART NO.)

POSITION #1 INDICATOR



- ① CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- ② USE WITH #26-#30 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- ③ THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- ④ POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5 FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103659
- ⑥ ASSEMBLIES ARE JOINED BY THE CARRIER STRIP.
ORDER QUANTITY REFLECTS TOTAL NUMBER OF
INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE
FOR NUMBER OF ASSEMBLIES PER STRIP.
- ⑦ MATERIAL— HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK
PINS: PHOS. BRONZE
- ⑧ FINISH— PINS: .000100—.000200 BRIGHT TIN—LEAD
OVER .000050 NICKEL.
- ⑨ FINISH— PINS: .000100—.000200 MATTE TIN
OVER .000050 NICKEL.
- ⑩ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	OBSOLETE		2	2.59	1.295	1-103653-1	12	6-103947-1
	OBSOLETE		2	2.39	1.195	1-103653-0	1 1	6-103947-0
	OBSOLETE		2	2.19	1.095	103653-9	10	5-103947-9
	OBSOLETE		2	1.99	.995	103653-8	9	5-103947-8
			2	1.79	.895	103653-7	8	5-103947-7
	OBSOLETE		3	2.39	.795	103653-6	7	5-103947-6
	OBSOLETE		2	1.39	.695	103653-5	6	5-103947-5
	OBSOLETE		4	2.38	.595	103653-4	5	5-103947-4
			4	1.98	.495	103653-3	4	5-103947-3
			5	1.98	.395	103653-2	3	5-103947-2
			8	2.36	.295	103653-1	2	5-103947-1
	OBSOLETE		2	2.59	1.295	1-103653-1	12	1-103947-1
	OBSOLETE		2	2.39	1.195	1-103653-0	1 1	1-103947-0
	OBSOLETE		2	2.19	1.095	103653-9	10	103947-9
	OBSOLETE		2	1.99	.995	103653-8	9	103947-8
	SUPERSEDED		2	1.79	.895	103653-7	8	103947-7
	OBSOLETE		3	2.39	.795	103653-6	7	103947-6
			2	1.39	.695	103653-5	6	103947-5
	OBSOLETE		4	2.38	.595	103653-4	5	103947-4
			4	1.98	.495	103653-3	4	103947-3
			5	1.98	.395	103653-2	3	103947-2
			8	2.36	.295	103653-1	2	103947-1
		PLATING		B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 26JUL00 CHK K WRIGHT 26JUL00 APVD K WRIGHT 26JUL00		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± -		NAME SHROUDED PIN ASSY, AMPMODU MTE, SINGLE ROW, .100 CL, POLARIZED, W/ LATCH WINDOWS, FOR #26-#30 AWG WIRE SIZE, STRIP FORM	
MATERIAL 		FINISH SEE TABLE		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-103947	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 of 1	
				REV 1	