

1) Antenna connection, 2) LED (CP), 3) LED (Power), 4) Read head connection X1, 5) Tightening torque



Basic features

Approval/Conformity	CE UKCA WEEE
Principle of operation	Converter

Display/Operation

Function indicator	Power (ON), LED green CP (Code tag present), LED yellow Operating, LED yellow flashing
--------------------	--

Electrical connection

Connection	Male, 4-pin
Connection slots	RCA-Female

Remarks

Only for data carriers acc. to ISO 15693 and ISO 14443A.
 Only together with BIS V-6xxx
 For basic equipment: Accessories see www.balluff.com
 Values are under rated conditions unless otherwise specified.
 Suitable for use with antennas BIS M-371-000-A01 and BIS M-372-000-A01

Environmental conditions

Ambient temperature	-20...50 °C
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
IP rating	IP65, with connector
Storage temperature	-20...70 °C


Material

Housing material	Aluminium
------------------	-----------

Mechanical data

Application weight	375.00 g
Dimension	112 x 48 x 97 mm

Connector Drawings



1) View towards connector