



- NOTES
- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, UL94V-0  
CONTACT: COPPER ALLOY  
RETENTION LEG: COPPER ALLOY
  - △6 FINISH (CONTACT AREA): 0.38μm PdNi & Au PLATING OVER NICKEL
  - △3 FINISH (CONTACT AREA): 0.76μm PdNi & Au PLATING OVER NICKEL
  - △4 FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
  - △5 FINISH (RETENTION LEG): TIN-LEAD PLATED (CONTACT TAIL) OVER NICKEL
  - △6 FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

△6 △4	-5
△6 △3	-3
△6 △2	316517-2
FINISH	型番 PART NUMBER

C	REVISED PER ECR-25-250788	FZ	R.B.	16 JAN 2025
B	REVISED (FJD0-0039-03)	TS	J.M.	07/25/03
A	REVISED (FJD0-0114-03)	TS	SM	25 APR '03
O	RELEASED FJ00-3261-95	NM	Y.I.	10/24 '95
LTR	変更 (REVISION RECORD)	DR	CHK	DATE

Copyright ©1995 年 日本エー・エス・ピー株式会社		Copyright ©1995 AMP (Japan), LTD. ALL RIGHTS RESERVED.	
適合電線範囲 (WIRE RANGE) mm <sup>2</sup> (AWG - )	被覆外径 (INSULATION DIA.) mm <sup>φ</sup>	名称 (NAME) DYNAMIC (D-3500) 20 POS. V HDR. ASS'Y	
材料 (MATERIAL) (SEE NOTE) 注記参照	仕上 (FINISH) (SEE NOTE) 注記参照	一般公差 (GENERAL TOLERANCE) 10mm以下 : ±0.35 10mm超 3mm以下 : ±0.4 30mm超 100mm以下 : ±0.45 角 度 : ±3'	LOC 番号 (No.) A3 J C-316517
DR. 24 OCT 95 N.MATSUBARA	DE. 24 OCT 95 N.MATSUBARA	尺度 (SCALE) 2/1	REV. SHEET C 1 of 1
CHK. 24 OCT 95 Y.ISHIKAWA	APP. 24 OCT 95 S.MANABE		



NUMBER 316517  
 METRIC  
 PROJ NO. 395-623  
 単位: 寸法 DIMENSIONS IN MM. DO NOT SCALE PRINT  
 PRINT DIST  
 AMP-J  
 REV.10/93