


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	REVISED PER ECR-16-014072	24OCT2016	RS	DR

D

C

B

A




AMP WIRE RANGE	E13288 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1

STAMP AMP 22-18* APPROX AS SHOWN
22-16 SPLICES ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPEC SAE AS7928
COMMERCIAL WIRE RANGE IS 22-16.
- 2

MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS.



100	LOOSE PIECE,BOX	8-330367-1
2500	TAPE&REEL	330367-2
1000	LOOSE PIECE	330367
QTY.	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX
		VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE, 0.26-1.65mm ² [509-3,260] CIR MILS SOLID OR STRANDED
TOOLING INFORMATION		
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 28JUN2016	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK ROHDE DANIEL F 28JUN2016				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SPLICE, BUTT, W/ SIGHT HOLE, SOLISTRAND™			
		APVD ROHDE DANIEL F 28JUN2016	PRODUCT SPEC			
			APPLICATION SPEC			
			WEIGHT -			
MATERIAL COPPER PER ASTM B-152 ANNEALED		FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545	SIZE A2			
			CAGE CODE 00779			
			DRAWING NO C-330367			
			RESTRICTED TO -			
			SCALE 10:1			
			SHEET 1 OF 1			
			REV D3			
			CUSTOMER DRAWING			