



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2017-12-18	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	177537-2	Amount	114.153	Version	-	Identity			
Manufacturer Item Name	2.5 M.I.S. POST HDR ASSY 2P	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	2.5 M.I.S HDR HSG 2P NATURAL				1.0	70.0	mg	
Material	2	PA66				1.0	70.0	mg	
Substance	3	Phosphoric acid, trimethyl ester	Supplier	512-56-1	0.05	1.0	0.035	mg	
Substance	3	Nitrogen compounds - ISO 1043-4 code #FR(30)	Supplier	1043-4-FR30	9.0	1.0	6.3	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	2.1	mg	
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	87.95	1.0	61.565	mg	
Sub-Item	1	METRIC INTER. SYSTEM ROUND PIN				2.0	22.0765	mg	
Material	2	Brass				2.0	22.0	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.044	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.0022	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.5226	2.0	7.81497	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	2.0	0.022	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	2.2E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	2.0	0.011	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	2.0	0.011	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	2.0	14.08	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	2.0	2.2E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	2.0	0.002178	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	2.0	0.011	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.1E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.0011	mg	

Material	2	Tin Plate				2.0	0.0765	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	2.0	5.355E-5	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	1.53E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	2.0	0.07629345	mg	