



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-01-08	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	5650090-7	Amount	6487.209284	Version	-	Identity			
Manufacturer Item Name	CONNECTOR ASSEMBLY, DUAL POSITIONS, .050	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	AMP 50CL HSG 23 DUAL POS				1.0	5153.4	mg	
Material	2	PCT-GF40				1.0	5153.4	mg	
Substance	3	9,10-Anthracenedione, 1,1-[(6-phenyl-1,3,5-triazine-2,4-dyl)diimino]bis-	Supplier	4118-16-5	0.188	1.0	9.68839	mg	
Substance	3	Formaldehyde, polymer with 2-(chloromethyl)oxirane and 2-methylphenol	Supplier	29690-82-2	0.4	1.0	20.6136	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	40.0	1.0	2061.36	mg	
Substance	3	2,4,8,10-Tetraoxa-3,9-diphosphaspiro[5.5]undecane, 3,9-bis[2,4-bis(1,1-dimethylethyl)phenoxy]-	Supplier	26741-53-7	0.2	1.0	10.3068	mg	
Substance	3	12H-Phthaloperin-12-one, 8,9,10,11-tetrachloro-	Supplier	20749-68-2	0.1155	1.0	5.95218	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	10.3068	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.0488	1.0	2.51486	mg	

Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0217	3.8477	1.0	198.28737	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-cyclohexanedi methanol	Supplier	25135-20-0	40.0	1.0	2061.36	mg	
Substance	3	Benzene, ethenyl-, homopolymer, brominated	Supplier	88497-56-7	12.0	1.0	618.408	mg	
Substance	3	Antimonate (SbO31-), sodium (1:1)	Supplier	15432-85-6	3.0	1.0	154.602	mg	
Sub-Item	1	CONTACT, .050 SERIES, STANDARD EDGE				23.0	28.995854	mg	
Material	2	Phos Bronze				23.0	28.3	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	23.0	0.00566	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1485	23.0	26.36103	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	23.0	0.0849	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	23.0	0.00283	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	23.0	0.09905	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	23.0	0.0283	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	23.0	0.001415	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	23.0	2.83E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	23.0	0.0283	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	23.0	0.00283	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	23.0	1.6414	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	23.0	0.001415	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	23.0	1.415E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	23.0	0.01415	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	23.0	0.0283	mg	
Material	2	Tin Plate				23.0	0.1455	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	23.0	2.91E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	23.0	0.14511	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	23.0	1.0185E-4	mg	
Material	2	Nickel Plate				23.0	0.54003	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	23.0	5.4003E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	23.0	0.00108006	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	23.0	0.53841	mg	
Material	2	Gold Plate				23.0	0.0103239	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	23.0	0.01029293	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	23.0	3.09717E-5	mg	
Sub-Item	1	CONTACT, .050 SERIES, STANDARD EDGE				23.0	28.995854	mg	
Material	2	Phos Bronze				23.0	28.3	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	23.0	0.00566	mg	
Substance	3	Copper	Supplier	7440-50-8	93.1485	23.0	26.36103	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	23.0	0.0849	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	23.0	0.00283	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.35	23.0	0.09905	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	23.0	0.0283	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0050	23.0	0.001415	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	23.0	2.83E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	23.0	0.0283	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	23.0	0.00283	mg	
Substance	3	Tin	Supplier	7440-31-5	5.8	23.0	1.6414	mg	

Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	23.0	0.001415	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	23.0	1.415E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	23.0	0.01415	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	23.0	0.0283	mg	
Material	2	Tin Plate				23.0	0.1455	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	23.0	2.91E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	23.0	0.14511	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	23.0	1.0185E-4	mg	
Material	2	Nickel Plate				23.0	0.54003	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	23.0	5.4003E-4	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	23.0	0.00108006	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	23.0	0.53841	mg	
Material	2	Gold Plate				23.0	0.0103239	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	23.0	0.01029293	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	23.0	3.09717E-5	mg	