



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Wu, Cc	Contact Title	Engineer Product Compliance china		
Company Unique ID	TE Connectivity	Response Date	2018-02-08	Contact Email	cc.wu@te.com				
Contact Phone Number	86-2124071672								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-640457-0	Amount	1432.26969558	Version	-	Identity			
Manufacturer Item Name	10P MTA100 HDR ASSY SQ R/A F/L	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	MTA100 HDR EXTRU FR LOK NATL				1.0	736.459	mg	
Material	2	PBT				1.0	736.459	mg	
Substance	3	Benzenepropionic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	1.47292	mg	
Substance	3	Ethene, homopolymer	Supplier	9002-88-4	5.0	1.0	36.82295	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.1	1.0	0.73646	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	8.0	1.0	58.91672	mg	
Substance	3	7-Oxabicyclo[4.1.0]heptane-3-carboxylic acid, 7-oxabicyclo[4.1.0]hept-3-ylmethyl ester	Supplier	2386-87-0	0.1	1.0	0.73646	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	3.68229	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.1	1.0	0.73646	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.5	1.0	3.68229	mg	

Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	156042-31-8	30.0	1.0	220.9377	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	5.0	1.0	36.82295	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.0	1.0	14.72918	mg	
Substance	3	Phosphorous acid, decyl diphenyl ester	Supplier	3287-06-7	0.1	1.0	0.73646	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	48.4	1.0	356.44616	mg	
Sub-Item	1	Brass Square				1.0	695.81069558	mg	
Material	2	Brass Wire				1.0	685.9128987	mg	
Substance	3	Copper	Supplier	7440-50-8	71.5	1.0	490.42772	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	0.00685913	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	1.0	192.21063	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	1.0	0.34296	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	0.00685913	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	1.0	0.34296	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.68591	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	1.0	0.06790538	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.06859129	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	1.0	0.34296	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	1.0	0.03429564	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	0.00342956	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	1.0	1.37183	mg	
Material	2	Nickel Plate				1.0	2.86165811	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.00572332	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.00286166	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	2.85307	mg	
Material	2	Tin Plate				1.0	7.03613877	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	0.01407228	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	1.0	7.01714	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	1.0	0.0049253	mg	