



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	Benfer, David W	<b>Contact Title</b>	Staff Mfg & Process Dvl Engineer		
<b>Company Unique ID</b>	TE Connectivity	<b>Response Date</b>	2018-03-14	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	+1-717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1055688-1	<b>Amount</b>	69.0000014	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>	2367 5001 54, VERT PLUG	<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
<b>EUREACH-0117</b>	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
<b>Complex Article Description</b>	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	2302 98 0154, SUB ASSY				1.0	69.0000014	mg	
Material	2	Gold Plate				1.0	0.767867	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.1	1.0	7.6787E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.9	1.0	0.7671	mg	
Material	2	Nickel Plate				1.0	0.3219624	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	1.0	6.4392E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	3.2196E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	1.0	0.321	mg	
Material	2	PPS-GF40				1.0	42.0	mg	
Substance	3	Benzene, 1,4-dichloro-, polymer with sodium sulfide (Na2S)	Supplier	26125-40-6	54.2	1.0	22.764	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	44.0	1.0	18.48	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	1.2	1.0	0.504	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.6	1.0	0.252	mg	
Material	2	Copper Alloy				1.0	25.910172	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	1.0	0.00259102	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	1.0	0.02591017	mg	
Substance	3	Zinc	Supplier	7440-66-6	13.0175	1.0	3.37286	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	1.0	0.00259102	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	1.0	2.591E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.25	1.0	0.06477543	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	1.0	2.591E-4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.5	1.0	0.12955	mg	
Substance	3	Copper	Supplier	7440-50-8	66.5	1.0	17.23026	mg	

Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	1.0	1.2955E-4	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	1.0	0.00259102	mg	
Substance	3	Nickel	Nickel	7440-02-0	19.5	1.0	5.05248	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	1.0	0.02591017	mg	