



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND		
Company Unique ID	TE Connectivity	Response Date	2018-06-20	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-5499913-1	Amount	13738.953676	Version	-	Identity			
Manufacturer Item Name	A/L UNIV HDR 60P RA SHT LAT	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EURoHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	A/L UNIV HDR CONT 15 DPLX				30.0	68.1576006	mg	
Material	2	Brass				30.0	66.79	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	30.0	0.06679	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	30.0	42.7456	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	30.0	0.033395	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	30.0	6.679E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	30.0	0.006679	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	30.0	0.06679	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	30.0	0.06679	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	30.0	23.51576	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	30.0	0.006679	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	30.0	0.006679	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	30.0	0.033395	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	30.0	0.20037	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	30.0	0.006679	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	30.0	3.3395E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	30.0	0.033395	mg	
Material	2	Nickel Plate				30.0	1.124267	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	30.0	0.00224853	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	30.0	0.00112427	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	30.0	1.12089	mg	
Material	2	Gold Flash				30.0	0.0473176	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	30.0	1.4195E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	30.0	0.04717565	mg	
Material	2	Gold Plate				30.0	0.043016	mg	

Substance	3	Gold	Supplier	7440-57-5	99.7	30.0	0.04288695	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	30.0	1.2905E-4	mg	
Material	2	Tin Plate				30.0	0.153	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	30.0	3.06E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	30.0	0.15259	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	30.0	1.071E-4	mg	
Sub-Item	1	A/L UNIV HDR CONT 15 DPLX				30.0	52.0541886	mg	
Material	2	Brass				30.0	50.891	mg	
Substance	3	Tin	Supplier	7440-31-5	0.1	30.0	0.050891	mg	
Substance	3	Copper	Supplier	7440-50-8	64.0	30.0	32.57024	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	30.0	0.0254455	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	30.0	5.0891E-4	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	30.0	0.0050891	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	30.0	0.050891	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.1	30.0	0.050891	mg	
Substance	3	Zinc	Supplier	7440-66-6	35.2085	30.0	17.91796	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	30.0	0.0050891	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	30.0	0.0050891	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.05	30.0	0.0254455	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.3	30.0	0.15267	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	30.0	0.0050891	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	30.0	2.5446E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	30.0	0.0254455	mg	
Material	2	Nickel Plate				30.0	0.919855	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	30.0	0.00183971	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	30.0	9.1986E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	30.0	0.9171	mg	
Material	2	Gold Flash				30.0	0.0473176	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	30.0	1.4195E-4	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	30.0	0.04717565	mg	
Material	2	Gold Plate				30.0	0.043016	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	30.0	0.04288695	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	30.0	1.2905E-4	mg	
Material	2	Tin Plate				30.0	0.153	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	30.0	3.06E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.73	30.0	0.15259	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	30.0	1.071E-4	mg	
Sub-Item	1	UNIVERSAL HEADER LATCH				2.0	397.2	mg	
Material	2	PBT-I-GF30-FR(17)				2.0	397.2	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	2.0	1.986	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	2.0	139.02	mg	

Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	2.0	0.7944	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	2.0	0.7944	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	2.0	11.916	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	2.0	7.944	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	2.0	3.972	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	2.0	1.986	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	2.0	3.972	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	2.0	145.3752	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	2.0	1.986	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	2.0	71.496	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	2.0	1.986	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	2.0	3.972	mg	
Sub-Item	1	UNV AMP-LATCH HDR HSG 60P W/MTG EARS				1.0	9338.2	mg	
Material	2	PBT-I-GF30-FR(17)				1.0	9338.2	mg	
Substance	3	Dolomite (CaMg(CO3)2)	Supplier	16389-88-1	0.5	1.0	46.691	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	35.0	1.0	3268.37	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.2	1.0	18.6764	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	18.6764	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	3.0	1.0	280.146	mg	
Substance	3	Talc (Mg3H2(SiO3)4)	Supplier	14807-96-6	2.0	1.0	186.764	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	1.0	1.0	93.382	mg	
Substance	3	Chlorite-group minerals	Supplier	1318-59-8	0.5	1.0	46.691	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	93.382	mg	

Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	36.6	1.0	3417.7812	mg	
Substance	3	Phosphoric acid, zinc salt (2:3)	Supplier	7779-90-0	0.5	1.0	46.691	mg	
Substance	3	Aromatic Brominated flame retardant with Antimony - ISO 1043-4 code #FR(17)	Supplier	1043-4-FR17	18.0	1.0	1680.876	mg	
Substance	3	Quartz (SiO2)	Supplier	14808-60-7	0.5	1.0	46.691	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	1.0	1.0	93.382	mg	