



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Staff Mfg & Process Dvl Engineer		
Company Unique ID	TE Connectivity	Response Date	2018-04-04	Contact Email	dave.benfer@te.com				
Contact Phone Number	+1-717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1-1478125-0	Amount	28876.126	Version	-	Identity			
Manufacturer Item Name	BNC R/A Plg WL 75Ohm Silver Pltd RG179B/	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirements by application of the selected exemption(s)								
ChinaRoHS-0508	Product(s) is NOT eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-0117	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Complex Article Description	REACH Candidate Substances of Very High Concern according to Once an Article Always an Article are Not Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Material	1	bushing-Ag plating				1.0	7.343	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	7.343	mg	
Material	1	Spring				1.0	200.0	mg	
Substance	2	Carbon	Supplier	7440-44-0	0.075	1.0	0.15	mg	
Substance	2	Sulfur	Supplier	7704-34-9	0.0020	1.0	0.0040	mg	
Substance	2	Nitrogen	Supplier	7727-37-9	0.65	1.0	1.3	mg	
Substance	2	Copper	Supplier	7440-50-8	0.21	1.0	0.42	mg	
Substance	2	Manganese	Supplier	7439-96-5	1.35	1.0	2.7	mg	
Substance	2	Iron	Supplier	7439-89-6	70.912	1.0	141.824	mg	
Substance	2	Phosphorus	Supplier	7723-14-0	0.031	1.0	0.062	mg	
Substance	2	Chromium	Supplier	7440-47-3	18.25	1.0	36.5	mg	
Substance	2	Silicon	Supplier	7440-21-3	0.44	1.0	0.88	mg	
Substance	2	Nickel	Nickel	7440-02-0	8.08	1.0	16.16	mg	
Material	1	Gasket				1.0	470.0	mg	
Substance	2	Iron	Supplier	7439-89-6	0.15	1.0	0.705	mg	
Substance	2	Copper	Supplier	7440-50-8	61.83	1.0	290.601	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.44	1.0	175.968	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	2.35	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	0.08	1.0	0.376	mg	
Material	1	Block ring				1.0	250.0	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.99	1.0	94.975	mg	
Substance	2	Copper	Supplier	7440-50-8	59.68	1.0	149.2	mg	
Substance	2	Iron	Supplier	7439-89-6	0.32	1.0	0.8	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.025	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	1.5	1.0	3.75	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	1.25	mg	
Material	1	Inner conductor				1.0	298.0	mg	
Substance	2	Iron	Supplier	7439-89-6	0.32	1.0	0.9536	mg	

Substance	2	Copper	Supplier	7440-50-8	59.68	1.0	177.8464	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.0298	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.99	1.0	113.2102	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	1.5	1.0	4.47	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	1.49	mg	
Material	1	End cap-Ag plating				1.0	5.69	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	5.69	mg	
Material	1	nut-Ni plating				1.0	35.271	mg	
Substance	2	Nickel	Nickel	7440-02-0	100.0	1.0	35.271	mg	
Material	1	bushing				1.0	1277.0	mg	
Substance	2	Copper	Supplier	7440-50-8	59.68	1.0	762.1136	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.99	1.0	485.1323	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.1277	mg	
Substance	2	Iron	Supplier	7439-89-6	0.32	1.0	4.0864	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	1.5	1.0	19.155	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	6.385	mg	
Material	1	End cap				1.0	956.0	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	4.78	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.0956	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.99	1.0	363.1844	mg	
Substance	2	Iron	Supplier	7439-89-6	0.32	1.0	3.0592	mg	
Substance	2	Copper	Supplier	7440-50-8	59.68	1.0	570.5408	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	1.5	1.0	14.34	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Material	1	Rubber Mat				1.0	50.0	mg	
Substance	2	Siloxanes and Silicones, di-Me, Me vinyl, vinyl group-terminated	Supplier	68083-18-1	78.0	1.0	39.0	mg	
Substance	2	Siloxanes and Silicones, di-Me, hydroxy-terminated	Supplier	70131-67-8	1.0	1.0	0.5	mg	
Substance	2	Silica	Supplier	7631-86-9	21.0	1.0	10.5	mg	
Material	1	Inner conductor Ag plating				1.0	3.09	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	3.09	mg	
Material	1	insulation				1.0	770.0	mg	
Substance	2	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	100.0	1.0	770.0	mg	
Material	1	Block ring-Ag plating				1.0	4.043	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	4.043	mg	
Material	1	body				1.0	14610.0	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	1.461	mg	
Substance	2	Copper	Supplier	7440-50-8	59.68	1.0	8719.248	mg	
Substance	2	Iron	Supplier	7439-89-6	0.32	1.0	46.752	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.99	1.0	5550.339	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	73.05	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	1.5	1.0	219.15	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Material	1	Gasket-Ag plating				1.0	5.079	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	5.079	mg	
Material	1	The fixed seat				1.0	5950.0	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.99	1.0	2260.405	mg	
Substance	2	Iron	Supplier	7439-89-6	0.32	1.0	19.04	mg	

Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.595	mg	
Substance	2	Copper	Supplier	7440-50-8	59.68	1.0	3550.96	mg	
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	29.75	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	1.5	1.0	89.25	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Material	1	nut				1.0	3900.0	mg	
Substance	2	Zinc	Supplier	7440-66-6	37.99	1.0	1481.61	mg	
Substance	2	Iron	Supplier	7439-89-6	0.32	1.0	12.48	mg	
Substance	2	Copper	Supplier	7440-50-8	59.68	1.0	2327.52	mg	
Substance	2	Antimony	Supplier	7440-36-0	0.01	1.0	0.39	mg	
Substance	2	Lead	Lead/Lead Compounds	7439-92-1	1.5	1.0	58.5	mg	6(c) Lead as an alloying element in copper containing up to 4% lead by weight
Substance	2	Nickel	Nickel	7440-02-0	0.5	1.0	19.5	mg	
Material	1	body-Ag plating				1.0	67.25	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	67.25	mg	
Material	1	The fixed seat-Ag plating				1.0	17.36	mg	
Substance	2	Silver	Supplier	7440-22-4	100.0	1.0	17.36	mg	